

CRIMPFOX-SC 1,5-M - Crimping pliers



1212725

<https://www.phoenixcontact.com/us/products/1212725>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Crimping pliers, for non-insulated slip-on sleeves 2.8 and 4.8 mm, 0.1 - 1.5 mm², B crimp



Your advantages

- Unlockable pressure lock
- Marked die stations for precise processing of corresponding cross sections
- Crimping pliers for uninsulated slip-on sleeves
- Consistently high crimping quality

Commercial data

Item number	1212725
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3134
GTIN	4046356857840
Weight per piece (including packing)	620.3 g
Weight per piece (excluding packing)	620.3 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-SC 1,5-M - Crimping pliers



1212725

<https://www.phoenixcontact.com/us/products/1212725>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Crimping tool
Compression	B crimp
Product property	Unlockable pressure lock
	Marked die stations
	Crimping pliers for uninsulated slip-on sleeves

Crimping position 1

Min. cross section	0.1 mm ²
Max. cross section	0.5 mm ²
AWG min	26
AWG max	20

Crimping position 2

Min. cross section	0.5 mm ²
Max. cross section	1 mm ²
AWG min	20
AWG max	18

Crimping position 3

Min. cross section	0.5 mm ²
Max. cross section	1.5 mm ²
AWG min	20
AWG max	16

Connection data

Conductor connection

Cross section range, metric	0.1 mm ² ... 1.5 mm ²
Cross section range AWG	26 ... 16

Dimensions

Width	22 mm
Height	76 mm
Length	204 mm

CRIMPFOX-SC 1,5-M - Crimping pliers



1212725

<https://www.phoenixcontact.com/us/products/1212725>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212725>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-SC 1,5-M - Crimping pliers



1212725

<https://www.phoenixcontact.com/us/products/1212725>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-SC 1,5-M - Crimping pliers



1212725

<https://www.phoenixcontact.com/us/products/1212725>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com