

UNIFOX-PC VDE_DB - Needle-nose pliers



1212811

<https://www.phoenixcontact.com/us/products/1212811>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Needle-nose pliers with cutter, 45° angle, notched gripping surface, VDE 1000 V AC/1500 V DC tested, type of packaging: with holder for sales display (backcard)

Your advantages

- For working on or in the vicinity of live parts up to 1000 V AC or 1500 V DC
- The tools feature ergonomic two-component safety handles
- Individually tested safety tools according to DIN EN 60900 (VDE 0682-201)

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212811 |
| Packing unit | 6 pc |
| Minimum order quantity | 6 pc |
| Sales key | BH31 |
| Product key | BH3162 |
| GTIN | 4046356994750 |
| Weight per piece (including packing) | 209 g |
| Weight per piece (excluding packing) | 209 g |
| Customs tariff number | 82032000 |
| Country of origin | DE |

UNIFOX-PC VDE_DB - Needle-nose pliers



1212811

<https://www.phoenixcontact.com/us/products/1212811>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Universal tools

Dimensions

Length

205 mm

Material specifications

Color

black

Standards and regulations

Tests

DIN EN 60900 (VDE 0682 PART 201)

DIN ISO 5745

UNIFOX-PC VDE_DB - Needle-nose pliers



1212811

<https://www.phoenixcontact.com/us/products/1212811>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212811>



EAC

Approval ID: RU x-DE.xx08.B.02974



VDE approval of drawings

Approval ID: 40052526

UNIFOX-PC VDE_DB - Needle-nose pliers



1212811

<https://www.phoenixcontact.com/us/products/1212811>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043816 |
| ECLASS-15.0 | 21043816 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000835 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27112100 |
|-------------|----------|

UNIFOX-PC VDE_DB - Needle-nose pliers



1212811

<https://www.phoenixcontact.com/us/products/1212811>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com