VS-15-ST-DSUB/16-MPT-0,5 - D-SUB contact insert

1688078

https://www.phoenixcontact.com/us/products/1688078

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



D-SUB contact insert, shell size 2, with 15 signal contacts, male type of contact, screw connection, straight, for panel mounting frame and sleeve housing with IP67 protection

Your advantages

- Screw connection

Commercial data

Item number	1688078
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAA
GTIN	4017918179564
Weight per piece (including packing)	17.27 g
Weight per piece (excluding packing)	15.1 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Product properties

Product type	Contact insert
Application	Combination contact insert
Type	D-SUB
Number of positions	15
Connection profile	D-SUB 15
Shielded	no

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	60 V
Rated current	5 A
Insulation resistance	≥ 5000 MΩ
Contact resistance per contact pair	≤ 2.5 mΩ
Transmission medium	Copper

Connection data

Connection method	Screw connection

Dimensions

Width	39.3 mm
Height	12.6 mm
Length	48 mm

Material specifications

Flammability rating according to UL 94	V0
Housing material	Steel
Housing surface material	tin-plated
Contact material	Copper alloy
Contact surface material	Au/Ni

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≤ 200
Insertion force per signal contact	≤ 3.30 N
Extraction force per signal contact	≤ 2.2 N

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 80 °C

Mounting

Mounting type	Hole

Drawings

Circuit diagram



Circuit diagram

Classifications

ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

ETIM

ETIM 10.0	EC001132

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	68c12945-45a9-433b-9009-2386a8d401bf

EF3.1 Climate Change

CO2e kg	1.203 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com