# ME B-SA/NS 35 GY - Cover

2202420

https://www.phoenixcontact.com/us/products/2202420

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Terminal cover, 1 strip covers up to 12 terminal points, for ME-BUS male side, (female side)



## Your advantages

- Easy, tool-free mounting
- Flammability rating V0 in accordance with UL 94

## Commercial data

| | |
|---|---|
| Item number | 2202420 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Note | Made to order (non-returnable) |
| Sales key | AC08 |
| Product key | ACHACZ |
| GTIN | 4055626113739 |
| Weight per piece (including packing) | 5.15 g |
| Weight per piece (excluding packing) | 4.55 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

# Technical data

## Product properties

| | |
|---|---|
| Product type | Filler plug |
| Housing type | DIN rail housing |
| Housing series | ME |
| Ventilation openings present | no |

## Dimensions

| | |
|---|---|
| Width | 14.5 mm |
| Height | 91.1 mm |
| Depth | 17.9 mm |
| Depth from top edge of DIN rail | 15.2 mm |

## Material specifications

| | |
|---|---|
| Color (Filler plug) | gray (RAL 7042) |
| Material Filler plug | PA |
| Flammability rating according to UL 94 | V0 |
| CTI according to IEC 60112 | 600 |

## Environmental and real-life conditions

### Ambient conditions

| | |
|---|---|
| Max. IP code to attain | IP20 |
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

## Mounting

| | |
|---|---|
| Mounting type | Snap in |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002779 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 31261500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 0.042 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com