

# CP-HC-S - Coding profile



1410916

<https://www.phoenixcontact.com/us/products/1410916>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Coding profile, for contact inserts HC-BB... / HC-A10... / HC-A16...



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1410916       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BF61          |
| Product key                          | AF7ABZ        |
| GTIN                                 | 4046356886567 |
| Weight per piece (including packing) | 0.83 g        |
| Weight per piece (excluding packing) | 0.82 g        |
| Customs tariff number                | 39269097      |
| Country of origin                    | CN            |

# CP-HC-S - Coding profile



1410916

<https://www.phoenixcontact.com/us/products/1410916>

## Technical data

### Product properties

|              |                |
|--------------|----------------|
| Product type | Coding element |
|--------------|----------------|

### Mounting

|               |  |
|---------------|--|
| Assembly note | 4 coding profiles per star, 10 stars per unit pack<br>for contact inserts HC-BB... / HC-A10... / HC-A16... |
|---------------|--|

### Material specifications

|  |    |
|--|----|
| Material                               | PA |
| Flammability rating according to UL 94 | V2 |
| Contact carrier material               | PA |
| Standards/regulations                  | PA |


# CP-HC-S - Coding profile

1410916

<https://www.phoenixcontact.com/us/products/1410916>



## Drawings



Dimensional drawing

# CP-HC-S - Coding profile



1410916

<https://www.phoenixcontact.com/us/products/1410916>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440203 |
| ECLASS-15.0 | 27440203 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002311 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CP-HC-S - Coding profile



1410916

<https://www.phoenixcontact.com/us/products/1410916>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.023 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)