

CUC-V14-A1ZNI-R45 - Panel-mount frame

1413988

<https://www.phoenixcontact.com/us/products/1413988>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

45° adapter for panel mounting frames



Commercial data

Item number	1413988
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNODZ
GTIN	4055626082356
Weight per piece (including packing)	82.5 g
Weight per piece (excluding packing)	79.85 g
Customs tariff number	85389099
Country of origin	DE

CUC-V14-A1ZNI-R45 - Panel-mount frame



1413988

<https://www.phoenixcontact.com/us/products/1413988>

Technical data

Product properties

Product type	Panel-mount frame
Type	Version 14

Insulation characteristics

Degree of pollution	2
---------------------	---

Dimensions

Width	40 mm
Height	54.8 mm
Length	49 mm

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
	NBR
Housing material	Die-cast zinc
Housing surface material	nickel-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 55 °C

CUC-V14-A1ZNI-R45 - Panel-mount frame



1413988

<https://www.phoenixcontact.com/us/products/1413988>

Classifications

ECLASS

ECLASS-13.0	27440210
ECLASS-15.0	27440210

ETIM

ETIM 10.0	EC002310
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-V14-A1ZNI-R45 - Panel-mount frame



1413988

<https://www.phoenixcontact.com/us/products/1413988>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com