

A-INR-PG16/13-N-NS-S - Reducing adapter



1415216

<https://www.phoenixcontact.com/us/products/1415216>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Reducing adapter, connecting thread: Pg16, color: silver-colored, with O-ring

Product description

Reduced Pg16 to Pg13,5

Commercial data

Item number	1415216
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF68
Product key	AF7DZX
GTIN	4055626038599
Weight per piece (including packing)	6.94 g
Weight per piece (excluding packing)	6.9 g
Customs tariff number	74198090
Country of origin	DE

A-INR-PG16/13-N-NS-S - Reducing adapter

1415216


<https://www.phoenixcontact.com/us/products/1415216>

Technical data

Product properties

Product type	Reducing adapter
Seal present	yes

Dimensions

Dimensional drawing	
Width	26.70 mm
Length	9.5 mm
Length of the connecting thread	6.5 mm
Length without connecting thread	3.5 mm
Diameter	37.5 mm
Connecting thread diameter	37.5 mm
Hexagon angular dimension	26.7 mm
Thread type connection side	Pg16
Thread type on seal side	Pg13,5

Material specifications

Color	brass color
Material	Brass, nickel-plated
Seal material O-ring	NBR
Housing surface material	Ni

Cable/line

Halogen-free	no
--------------	----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68 (Depends on the screw connection used)
----------------------	---


A-INR-PG16/13-N-NS-S - Reducing adapter

1415216

<https://www.phoenixcontact.com/us/products/1415216>

Drawings

Dimensional drawing



Dimensional drawing

A-INR-PG16/13-N-NS-S - Reducing adapter



1415216

<https://www.phoenixcontact.com/us/products/1415216>

Classifications

ECLASS

ECLASS-13.0	27140806
ECLASS-15.0	27140806

ETIM

ETIM 10.0	EC000938
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

1415216

<https://www.phoenixcontact.com/us/products/1415216>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	8b31dd34-031c-4d4d-905a-1afc9fc454be

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com