

# FOC-FR19:3U - 19" mounting frame



1419976

<https://www.phoenixcontact.com/us/products/1419976>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

19" mounting frame, design: 19" rack/fixed housing, degree of protection: IP20, material: Aluminum alloy, color: gray



## Product description

19" module rack for integration of 12 modules, 3 rack units

## Your advantages

- Modular enclosure design, up to 12 insert modules can be placed into 3U enclosure as required, in order to achieve high packing density FO connection
- The number of insert modules can be freely configured. For module vacancies, there are optional covers to be used with

## Commercial data

Item number	1419976
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB15
Product key	ABNHBC
GTIN	4055626198910
Weight per piece (including packing)	2,635 g
Weight per piece (excluding packing)	2,635 g
Customs tariff number	76169990
Country of origin	CN

# FOC-FR19:3U - 19" mounting frame



1419976

<https://www.phoenixcontact.com/us/products/1419976>

## Technical data

### Product properties

Product type	Network distributor box
Type	3RU
Number of slots	12

### Dimensions

Width	482.6 mm
Height	132 mm
Depth	220 mm

### Material specifications

Color	gray
Flammability rating according to UL 94	V0
Housing material	Aluminum alloy
Housing surface material	Powder-coated, gray

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
	IP20
	IP20

### Mounting

Mounting type	Screw mounting
---------------	----------------

# FOC-FR19:3U - 19" mounting frame



1419976

<https://www.phoenixcontact.com/us/products/1419976>

## Classifications

### ECLASS

ECLASS-13.0	19170192
ECLASS-15.0	19170192

### ETIM

ETIM 10.0	EC003626
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# FOC-FR19:3U - 19" mounting frame



1419976

<https://www.phoenixcontact.com/us/products/1419976>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)