

# SEALING PLUG 48X35 RD - Sealing plug



1425357

<https://www.phoenixcontact.com/us/products/1425357>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sealing plug, color: red



## Commercial data

Item number	1425357
Packing unit	5 pc
Minimum order quantity	5 pc
Note	Made to order (non-returnable)
Sales key	BF68
Product key	AF7DZX
GTIN	4055626394626
Weight per piece (including packing)	24.57 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	39235090
Country of origin	DE

# SEALING PLUG 48X35 RD - Sealing plug



1425357


<https://www.phoenixcontact.com/us/products/1425357>

## Technical data

### Product properties

Product type	Sealing plugs
--------------	---------------

### Dimensions

Dimensional drawing	
Length	35 mm
Diameter	47 mm

### Material specifications

Material	PA
----------	----

### Cable/line

Halogen-free	yes
--------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 100 °C
---------------------------------	-------------------

### Mounting

Assembly note	The head of the sealing plug must still be visible after mounting in the screw connection (see "after mounting" photo).
---------------	---

# SEALING PLUG 48X35 RD - Sealing plug




1425357

<https://www.phoenixcontact.com/us/products/1425357>

## Drawings

Dimensional drawing



Dimensional drawing

# SEALING PLUG 48X35 RD - Sealing plug



1425357

<https://www.phoenixcontact.com/us/products/1425357>

## Classifications

### ECLASS

ECLASS-13.0	23111190
ECLASS-15.0	27140805

### ETIM

ETIM 10.0	EC002610
-----------	----------

### UNSPSC

UNSPSC 21.0	39121300
-------------	----------

# SEALING PLUG 48X35 RD - Sealing plug



1425357

<https://www.phoenixcontact.com/us/products/1425357>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)