

# PROT-M12 FS-M - Sealing cap

1430488

<https://www.phoenixcontact.com/us/products/1430488>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M12 metal sealing cap for unoccupied M12 plugs of the sensor/actuator cable, flush-type plugs and I/O devices in the field

## Your advantages

- Reliable protection of unoccupied slots during transport and use in the field
- Robust and reliable: brass protective cap up to IP69K degree of protection
- Protected against splash water and dust by the internal seal
- Easy assembly by hand or using a wrench

## Commercial data

Item number	1430488
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB26
Product key	ABQEQA
GTIN	4046356325776
Weight per piece (including packing)	9.68 g
Weight per piece (excluding packing)	9.226 g
Customs tariff number	74198090
Country of origin	DE

# PROT-M12 FS-M - Sealing cap



1430488

<https://www.phoenixcontact.com/us/products/1430488>

## Technical data

### Notes

General	Use up to max. 48 V AC and 60 V DC
---------	------------------------------------

### Product properties

Product type	Protective cap
Thread type	M12

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C
---	------------------

# PROT-M12 FS-M - Sealing cap



1430488

<https://www.phoenixcontact.com/us/products/1430488>

## Classifications

### ECLASS

ECLASS-13.0	27440208
ECLASS-15.0	27440208

### ETIM

ETIM 10.0	EC002314
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# PROT-M12 FS-M - Sealing cap



1430488

<https://www.phoenixcontact.com/us/products/1430488>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)