

SACC-M12-KD-NUT-SH - EMC nut



1440151

<https://www.phoenixcontact.com/us/products/1440151>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

EMC nut, for threads M12 x 1, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)



Product description

EMC nut M12 required for shield contact with coated housing surfaces.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1440151 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | AB27 |
| Product key | ABQZBA |
| GTIN | 4046356483315 |
| Weight per piece (including packing) | 2.28 g |
| Weight per piece (excluding packing) | 2.25 g |
| Customs tariff number | 74153300 |
| Country of origin | DE |

SACC-M12-KD-NUT-SH - EMC nut



1440151

<https://www.phoenixcontact.com/us/products/1440151>

Technical data

Product properties

| | |
|--------------|----------|
| Product type | Flat nut |
| Thread type | M12 |

Dimensions

| | |
|-----------------------------|---------|
| Wrench size, counter nut | 15 mm |
| Thread type connection side | M12 x 1 |
| Thread pitch | 1 mm |

Material specifications

| | |
|----------------|---------|
| Material (Nut) | CuZn/Ni |
|----------------|---------|

SACC-M12-KD-NUT-SH - EMC nut



1440151

<https://www.phoenixcontact.com/us/products/1440151>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440210 |
| ECLASS-15.0 | 27440210 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002310 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SACC-M12-KD-NUT-SH - EMC nut



1440151

<https://www.phoenixcontact.com/us/products/1440151>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com