

RC-12P1N120000 - Contact insert



1596856

<https://www.phoenixcontact.com/us/products/1596856>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 12, contact connection type: Pin, Solder cup, series: RC, CA, NC, RM, TU, UC, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1596856
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFU
GTIN	4046356212960
Weight per piece (including packing)	9.12 g
Weight per piece (excluding packing)	6.52 g
Customs tariff number	85366990
Country of origin	DE

RC-12P1N120000 - Contact insert



1596856

<https://www.phoenixcontact.com/us/products/1596856>

Technical data

Product properties

Product type	Contact insert
Series	RC
	CA
	NC
	RM
	TU
	UC
Application	Signal
Number of positions	12
Connection profile	12
No. of control contacts	12
Coding	N
Thread type	M23

Electrical properties

Contact: Contact group 1

Contact diameter	1 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Nominal current I _N	8 A (for max. connection cross section)
Nominal voltage U _N	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Connection method	Solder cup
-------------------	------------

Material specifications

Material Insulating body	PBT
Material Contact	CuZn
Material Contact surface	Ni/Au

Connector

Direction of rotation	Standard
-----------------------	----------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	100
-----------------------------	-----

RC-12P1N120000 - Contact insert



1596856

<https://www.phoenixcontact.com/us/products/1596856>

Drawings

Schematic diagram



Connector pin assignment

RC-12P1N120000 - Contact insert



1596856

<https://www.phoenixcontact.com/us/products/1596856>

Schematic diagram



Dimensional drawing

RC-12P1N120000 - Contact insert



1596856

<https://www.phoenixcontact.com/us/products/1596856>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-12P1N120000 - Contact insert



1596856

<https://www.phoenixcontact.com/us/products/1596856>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com