

# RC-06P1N122D00 - Device connector front mounting



1593109

<https://www.phoenixcontact.com/us/products/1593109>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, application: Signal, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Pin, Solder cup, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240332

## Commercial data

Item number	1593109
Packing unit	40 pc
Minimum order quantity	40 pc
Note	Made to order (non-returnable)
Product key	ABRAFL
GTIN	4046356194327
Weight per piece (including packing)	28.77 g
Weight per piece (excluding packing)	25.56 g
Country of origin	DE

1593109

<https://www.phoenixcontact.com/us/products/1593109>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
Thread type	M23

### Material specifications

Flammability rating according to UL 94	V0
--	----

### Connection data

#### Conductor connection

Connection method	Solder connection
-------------------	-------------------

### Connector

#### Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	6
Direction of rotation	Standard
Connection profile	6
Number (Contact group 1)	6
Litz wires Min. cross section (Contact group 1)	0.08 mm <sup>2</sup>
Litz wires Max. cross section (Contact group 1)	2.5 mm <sup>2</sup>
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3


### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP67
----------------------	------

Drawings

Schematic diagram



Connector pin assignment

Schematic diagram



Dimensional drawing

# RC-06P1N122D00 - Device connector front mounting



1593109

<https://www.phoenixcontact.com/us/products/1593109>

## Classifications

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1593109

<https://www.phoenixcontact.com/us/products/1593109>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	3b03c20a-1323-46fe-9a9e-9f05ef88cedf

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)