

# HC-D 7-KML-61/O1PG11 - Housing



1672893

<https://www.phoenixcontact.com/us/products/1672893>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupling housing, with single locking latch, height 61 mm, without screw connection, 1 x Pg11, zinc die-cast

The figure shows version HC-D 7-KML-51/M1PG11/ALU

## Commercial data

Item number	1672893
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF55
Product key	AF7AAE
GTIN	4017918145408
Weight per piece (including packing)	89.3 g
Weight per piece (excluding packing)	83 g
Customs tariff number	85389099
Country of origin	DE

# HC-D 7-KML-61/O1PG11 - Housing

1672893


<https://www.phoenixcontact.com/us/products/1672893>

## Technical data

### Product properties

Product type	Housing with locking latch
Housing type	Coupling housings
Application	Standard
Type	D7
No. of cable outlets	1
Type of the screw connection	1x Pg11
Cable outlet	straight
Pg screw connection	none

### Dimensions

Dimensional drawing	
Width	34 mm
Height	60.5 mm
Length	26.5 mm

### Material specifications

Housing material	Die-cast zinc
Housing surface material	Powder-coated, gray
Locking latch material	Steel, galvanized

### Mechanical properties

#### Mechanical data

Type of the screw connection	1x Pg11
------------------------------	---------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP54
	IP65 (with sealing screw)
Ambient temperature (operation)	-40 °C ... 125 °C

# HC-D 7-KML-61/O1PG11 - Housing


1672893

<https://www.phoenixcontact.com/us/products/1672893>



## Drawings

Dimensional drawing



Dimensional drawing

# HC-D 7-KML-61/O1PG11 - Housing



1672893

<https://www.phoenixcontact.com/us/products/1672893>

## Classifications

### ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

# HC-D 7-KML-61/O1PG11 - Housing



1672893

<https://www.phoenixcontact.com/us/products/1672893>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)