

## Crimping pliers - CRIMPFOX-1,6-ER-1,50-AT - 1884843


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers for rolled contacts CK 1.6-ER... and ...-BR..., 0.5 - 1.5 mm<sup>2</sup>



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 170073
GTIN	4017918170073

### Technical data

#### Dimensions

Length (b)	200 mm
------------	--------

#### General

Compression	universal
Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	1.5 mm <sup>2</sup>


#### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"


### Drawings

# Crimping pliers - CRIMPFOX-1,6-ER-1,50-AT - 1884843

Product drawing



Product drawing



## Classifications

### eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 11.0	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 9.0	21043811

### ETIM

ETIM 2.0	EC000384
ETIM 3.0	EC000384
ETIM 4.0	EC000385
ETIM 6.0	EC000168
ETIM 7.0	EC000168

### UNSPSC

UNSPSC 6.01	27112301
UNSPSC 7.0901	27112301
UNSPSC 11	27112301
UNSPSC 12.01	27112301
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

## Approvals

### Approvals

## Crimping pliers - CRIMPFOX-1,6-ER-1,50-AT - 1884843

### Approvals

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

---

Phoenix Contact 2021 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>