

UM 72-PROFIL L6,65CM GN VPE50 - Profile



2199838

<https://www.phoenixcontact.com/us/products/2199838>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Latching with side elements, latching with foot element, Basic profile, profile width (internal): 71.9 mm, profile width (external): 86.8 mm, length: 6.65 mm, depth: 21.5 mm



The figure shows the variant UM 45-Profil CM

Commercial data

Item number	2199838
Packing unit	50 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	ACHDBA
GTIN	4046356416894
Weight per piece (including packing)	31.606 g
Weight per piece (excluding packing)	26.7 g
Customs tariff number	39162000
Country of origin	DE

UM 72-PROFIL L6,65CM GN VPE50 - Profile



2199838

<https://www.phoenixcontact.com/us/products/2199838>

Technical data

Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing type	Extruded profile housings
Housing series	UM
Product family	UM72
Ventilation openings present	no

Dimensions

Depth	21.5 mm
Length	6.65 mm

External dimensions

Profile width (external)	86.8 mm
--------------------------	---------

Internal dimensions

Profile width (internal)	71.9 mm
--------------------------	---------

Material specifications

Color (Housing)	green (RAL 6021)
Material Housing	PVC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-15 °C ... 50 °C
---------------------------------	------------------

PCB data

Number of PCB holders	2
-----------------------	---

Mounting

Mounting type	Latching with side elements, latching with foot element
---------------	---------------------------------------------------------

UM 72-PROFIL L6,65CM GN VPE50 - Profile



2199838

<https://www.phoenixcontact.com/us/products/2199838>

Classifications

ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM 72-PROFIL L6,65CM GN VPE50 - Profile



2199838

<https://www.phoenixcontact.com/us/products/2199838>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com