

ME-IO 18,8 F-LR 7035 - Filler plug

2202635

<https://www.phoenixcontact.com/us/products/2202635>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Filler plug, for closing the Lock and Release area, width: 11.7 mm, height: 16.1 mm, depth: 10.6 mm, color: light gray (similar RAL 7035)

Your advantages

- Plastic in accordance with UL94 V0: for more rigorous flammability requirements
- Cover for fully closed device fronts
- Filler plugs for fully closed device fronts

Commercial data

Item number	2202635
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC15
Product key	ACHECZ
GTIN	4055626218748
Weight per piece (including packing)	0.81 g
Weight per piece (excluding packing)	0.8 g
Customs tariff number	39269097
Country of origin	CN

ME-IO 18,8 F-LR 7035 - Filler plug



2202635

<https://www.phoenixcontact.com/us/products/2202635>

Technical data

Product properties

Product type	Filler plug
Housing type	DIN rail housing
Housing type	Multifunctional housings
Housing series	ME-IO
Product family	ME-IO 18,8
Ventilation openings present	no

Dimensions

Width	11.7 mm
Height	16.1 mm
Depth	10.6 mm

Material specifications

Color (Filler plug)	light gray (RAL 7035)
Material Filler plug	PA
Flammability rating according to UL 94	V0
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Latching
---------------	----------

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

ME-IO 18,8 F-LR 7035 - Filler plug



2202635

<https://www.phoenixcontact.com/us/products/2202635>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2202635>



UL Recognized

Approval ID: E240868

ME-IO 18,8 F-LR 7035 - Filler plug



2202635

<https://www.phoenixcontact.com/us/products/2202635>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME-IO 18,8 F-LR 7035 - Filler plug



2202635

<https://www.phoenixcontact.com/us/products/2202635>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com