

2700950

<https://www.phoenixcontact.com/us/products/2700950>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Upgrade license for upgrading from WebVisit 6 Basic to WebVisit 6 Pro



## Product description

In addition to the basic functions, the Pro version of WebVisit contains the following macros:

- User level management
- Pointer tool
- URL jumps
- Alarm generation
- Trending
- Animated GIFs

## Your advantages

- Engineering tool used to create web visualizations for all controllers with integrated web server
- The visualization pages are displayed in any standard browser
- No programming knowledge is necessary for the creation of visualization pages
- Macro library with functions such as alarm lists, trends, a user management feature, URL jumps, etc.

## Commercial data

Item number	2700950
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR13
Product key	DRDABA
GTIN	4046356661249
Weight per piece (including packing)	25 g
Weight per piece (excluding packing)	24.999 g
Customs tariff number	49119900
Country of origin	DE

2700950

<https://www.phoenixcontact.com/us/products/2700950>

## Technical data

### Product properties

Product type	Visualization
--------------	---------------

### System properties

Control system	(Target system) Embedded controller
Type of software	On-premises
Intended use for the software	Web editor

### License information

Type of license	Single-user license
	Freeware
	Upgrade license
Information regarding the type of license	Upgrade from WebVisit BASIC to WebVisit PRO

### Functionality

Basic functions	The user interface has a functional design and even the basic version offers numerous graphic basic elements and functions.
	The variables needed for visualization are imported directly from PC Worx.
Integrated function	Trending
	Alarming
Programming languages supported	HTML5
Control system	(Target system) Embedded controller
Associated hardware	Phoenix Contact control
Number of I/O nodes	128000

### System requirements

Operating equipment	Keyboard, mouse
Operating system	Windows® 10 (32-bit/64-bit), as of Build 1511
	Windows®11, as of Build 22000.675
Hard disk memory	min. 2 GByte
Supported browsers	Internet Explorer Version 7 or later
	Internet Explorer Version 8 or later
	Internet Explorer Version 10 or later
	Mozilla Firefox Version 44 or later (recommended)
	Google Chrome Version 48 or later (recommended)
	Opera Version 11.64 or later
Languages supported	German, English, French
Screen resolution	1024 x 768 pixel(s) (XGA)

### Visualization properties

Alarming	yes
Trending	yes

2700950

<https://www.phoenixcontact.com/us/products/2700950>

## Classifications

### ECLASS

ECLASS-13.0	27242502
ECLASS-15.0	27242502

### ETIM

ETIM 10.0	EC001416
-----------	----------

### UNSPSC

UNSPSC 21.0	43231500
-------------	----------

2700950

<https://www.phoenixcontact.com/us/products/2700950>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.039 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)