

# VL PORTICO SERVER 4 CLIENT - Software



2701455

<https://www.phoenixcontact.com/us/products/2701455>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Remote network portal software. Allows remote control/viewing from up to four simultaneously connected remote client PCs.

## Product description

Portico is a remote control software product to view and fully interact with the desktop of another electronic device over a network. The product employs a client/server architecture that provides the ability to either establish point-to-point communication between a single device and single client, or to serve up the desktop of a single device to many clients. A control arbitration scheme ensures that only a single client has control of a device at any given time. In a manufacturing environment, Portico can be used to provide visibility and control to a machine or process from a remote location within the plant. Portico can also be used by an OEM to remotely troubleshoot a customer machine or process over the internet.

## Commercial data

Item number	2701455
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR12
Product key	DRBAAH
GTIN	4046356771153
Weight per piece (including packing)	143.3 g
Weight per piece (excluding packing)	140 g
Customs tariff number	85234910
Country of origin	US

2701455

<https://www.phoenixcontact.com/us/products/2701455>

## Technical data

### Product properties

Product type	Remote control software
--------------	-------------------------

### System properties

Intended use for the software	Remote desktop control
-------------------------------	------------------------

### License information

Type of license	Activation
-----------------	------------

### Functionality

Basic functions	Remote control software
-----------------	-------------------------

### System requirements

Operating system	Windows® 7
	Windows® 10
Processor	Atom™ or above
Hard disk memory	≥ 100 Mbyte (minimum (client and server))
Interfaces	≥100 Mbps Ethernet LAN
Languages supported	German, English, French, Spanish, Italian

# VL PORTICO SERVER 4 CLIENT - Software



2701455

<https://www.phoenixcontact.com/us/products/2701455>

## Classifications

### ECLASS

ECLASS-13.0	27242590
ECLASS-15.0	27242590

### ETIM

ETIM 10.0	EC001435
-----------	----------

### UNSPSC

UNSPSC 21.0	43233600
-------------	----------

# VL PORTICO SERVER 4 CLIENT - Software



2701455

<https://www.phoenixcontact.com/us/products/2701455>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)