

# PSD-S MUX SET/UL - Wireless elements



2701566

<https://www.phoenixcontact.com/us/products/2701566>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wireless multiplexer set with C-UL-US approval for mirroring the status of a signal tower to **one** other signal tower; set consists of a master with external antenna and a slave with internal antenna, 24 V AC/DC, black

## Your advantages

- Existing signal towers can be extended without additional wiring
- Can be operated parallel to other wireless applications
- Range of a wireless element with a free line of sight of up to 300 m

## Commercial data

Item number	2701566
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR07
Product key	DRL115
GTIN	4046356801966
Weight per piece (including packing)	102.2 g
Weight per piece (excluding packing)	102.2 g
Customs tariff number	85318095
Country of origin	DE

2701566

<https://www.phoenixcontact.com/us/products/2701566>

## Technical data

### Product properties

Product type	Wireless element
Scope of supply	1 transmitter module (slave) and 1 receiver module (master)
Number of mountable signal elements	4 (on both master and slave)

### Interfaces


#### Functions

Wireless licenses	USA, Canada
Country support	USA
	Canada

#### Wireless

Modulation type	2 FSK
Frequency	913 MHz
Frequency band	915 MHz
Transmission power	10 dBm (at 50 Ohm)
Range	max. 300 m
Transmission speed	38.4 kbps

### Dimensions

Dimensional drawing	
Height	65.5 mm
Diameter	70 mm
Note on dimensions	with perpendicular antenna: width 104 mm, height 189 mm

### Material specifications

Color	black
Material	Polycarbonate PC

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65 (when installed or with end cover)
Ambient temperature (operation)	-20 °C ... 50 °C

# PSD-S MUX SET/UL - Wireless elements



2701566

<https://www.phoenixcontact.com/us/products/2701566>

## EMC data


Electromagnetic compatibility	Conforms with guidelines: FCC Part 15.249/IC: RSS-210 Issue 8, RSS-GEN Issue 4, RSS-102 Issue 4
-------------------------------	---

## Mounting


Assembly note	Rubber seal pre-installed for each element
Mounting position	The master and slave are the bottom element in the signal tower

## Drawings

### Dimensional drawing



Dimensional drawing



# PSD-S MUX SET/UL - Wireless elements



2701566

<https://www.phoenixcontact.com/us/products/2701566>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)