

# FL NETWORK MANAGER BASIC - Network management software



2702889

<https://www.phoenixcontact.com/us/products/2702889>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SNMP-based software for easy commissioning and monitoring of network components such as switches, routers, and WLAN access points

## Your advantages

- All required services, such as BootP and TFTP server, included
- Rapid network startup thanks to multi-device configuration
- Also suitable for PROFINET switches, thanks to DCP support
- Non-proprietary use also possible, thanks to SNMP and FDCML standard
- Special support for Phoenix Contact Factoryline devices

## Commercial data

Item number	2702889
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN21
Product key	DNN155
GTIN	4055626379463
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	0.001 g
Customs tariff number	85234920
Country of origin	DE

# FL NETWORK MANAGER BASIC - Network management software



2702889

<https://www.phoenixcontact.com/us/products/2702889>

## Technical data

### Product properties

Product type	Network management software
--------------	-----------------------------

### System properties

Type of software	On-premises
Intended use for the software	Network configuration

### License information

Type of license	Single-user license
-----------------	---------------------

### Functionality

Basic functions	Network configuration
	Firmware update
	IP assignment via BootP, DHCP, DCP
	Handling of configuration files
	Multi-device configuration
	SNMP scripting
	Network representation
	VLAN configuration assistant
Offline configuration	
Expanded functionality	The FL Network Manager is not limited to a maximum number of nodes
Associated hardware	Ethernet infrastructure components

### System requirements

Operating equipment	Keyboard, mouse
Operating system	Windows® 10 (64 bit) from version 20H2, Windows® 11 from version 21H2
Note about the operating system	.NET Framework 4.8 required
Hard disk memory	min. 1 GByte
Network card	Correctly configured ETHERNET network card with TCP/IP protocol stack
Interfaces	Ethernet Port
Languages supported	German, English

# FL NETWORK MANAGER BASIC - Network management software



2702889

<https://www.phoenixcontact.com/us/products/2702889>

## Classifications

### ECLASS

ECLASS-13.0	19240201
ECLASS-15.0	19240201

### ETIM

ETIM 10.0	EC000501
-----------	----------

### UNSPSC

UNSPSC 21.0	43232900
-------------	----------

# FL NETWORK MANAGER BASIC - Network management software



2702889

<https://www.phoenixcontact.com/us/products/2702889>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)