

# ZBN 18:UNBEDRUCKT - Zack marker strip



2809128

<https://www.phoenixcontact.com/us/products/2809128>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, white (RAL 9010), unmarked, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: latching, for terminal block width: 18 mm, Number of individual labels: 5, text field height: 5 mm, text field width: 18 mm

## Your advantages

- Consists of five individual labels with 17.5 mm pitch
- Flat zack marker strips

## Commercial data

Item number	2809128
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2112
GTIN	4017918076245
Weight per piece (including packing)	0.83 g
Weight per piece (excluding packing)	0.8 g
Customs tariff number	39269097
Country of origin	PL

# ZBN 18:UNBEDRUCKT - Zack marker strip



2809128

<https://www.phoenixcontact.com/us/products/2809128>

## Technical data

### Product properties

Product type	Terminal marker
Pitch	18 mm

### Marking

Number of individual labels	5
Number of individual labels per row	5
Number of marker strips	10

### Dimensions

Width	17.00 mm
Height	6.60 mm
Depth	1.60 mm
Pitch	18 mm

### Text field

Text field width	18 mm
Text field height	5 mm

### Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

### Mounting

Mounting type	latching
---------------	----------

# ZBN 18:UNBEDRUCKT - Zack marker strip



2809128

<https://www.phoenixcontact.com/us/products/2809128>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# ZBN 18:UNBEDRUCKT - Zack marker strip



2809128

<https://www.phoenixcontact.com/us/products/2809128>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.006 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)