

# BRIDGE- 8-3M - Bridge

2901700

<https://www.phoenixcontact.com/us/products/2901700>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

3-phase loop bridge for 8 CONTACTRON modules, with screw connection and 22.5 mm housing width, connecting cable: 3 m



## Your advantages

- Only suitable for CONTACTRON series with screw connection ELR H3...-SC-..., ELR H5...-SC-..., EMM...IFS
- Bridging of 2 to 10 devices with maximum module spacing of 22.5 mm
- Considerable reduction in wiring
- Up to 575 V AC/3 x 25 A

## Commercial data

Item number	2901700
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C470
Product key	DK74Z1
GTIN	4046356624695
Weight per piece (including packing)	390.06 g
Weight per piece (excluding packing)	383.65 g
Customs tariff number	85444290
Country of origin	DE

# BRIDGE- 8-3M - Bridge

2901700

<https://www.phoenixcontact.com/us/products/2901700>



## Technical data

### Product properties

Product type	Loop bridge
Product family	CONTACTRON
Number of bridgeable modules	8

### Electrical properties

Operating voltage range	42 V AC ... 575 V AC
Operating current	≤ 25 A

### Connection data

Connection method	Screw connection
-------------------	------------------

### Dimensions

Width	22.5 mm
-------	---------

### Material specifications

Color	gray (RAL 7042)
-------	-----------------

### Cable/line

Connecting cable length	3 m
Cable cross section	2.5 mm <sup>2</sup>

# BRIDGE- 8-3M - Bridge

2901700

<https://www.phoenixcontact.com/us/products/2901700>



## Drawings




Figure shows the version BRIDGE- 4

# BRIDGE- 8-3M - Bridge



2901700

<https://www.phoenixcontact.com/us/products/2901700>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2901700>



**UL Listed**

Approval ID: FILE E 172140



**cUL Listed**

Approval ID: FILE E 172140



**cUL Listed**

Approval ID: E228652



**UL Listed**

Approval ID: E228652

# BRIDGE- 8-3M - Bridge

2901700

<https://www.phoenixcontact.com/us/products/2901700>



## Classifications

### ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

### ETIM

ETIM 10.0	EC002886
-----------	----------

### UNSPSC

UNSPSC 21.0	39121100
-------------	----------

# BRIDGE- 8-3M - Bridge

2901700

<https://www.phoenixcontact.com/us/products/2901700>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)