# BRIDGE-PT  2 - Bridge

2904490

https://www.phoenixcontact.com/us/products/2904490

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



3-phase loop bridge for 2 CONTACTRON modules, with Push-in connection and 22.5 mm housing width, connecting cable: 3 m

## Your advantages

- Bridging of 2 to 10 devices with maximum module spacing of 22.5 mm
- Up to 575 V AC/3 x 25 A

## Commercial data

| | |
|---|---|
| Item number | 2904490 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C470 |
| Product key | DK74Z1 |
| GTIN | 4046356842655 |
| Weight per piece (including packing) | 301.5 g |
| Weight per piece (excluding packing) | 283.9 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Loop bridge |
| Product family | CONTACTRON |
| Number of bridgeable modules | 2 |

### Electrical properties

| | |
|---|---|
| Operating voltage range | 42 V AC ... 575 V AC |
| Operating current | ≤ 25 A |

### Material specifications


| | |
|---|---|
| Color | gray (RAL 7042) |

### Cable/line

| | |
|---|---|
| Connecting cable length | 3 m |
| Cable cross section | 2.5 mm² |

## Drawings

Application drawing



## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2904490

**UL Listed**
Approval ID: FILE E 172140

**cUL Listed**
Approval ID: FILE E 172140

**cUL Listed**
Approval ID: E228652

**UL Listed**
Approval ID: E228652

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27371392 |
| ECLASS-15.0 | 27371392 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002886 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121100 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com