

FUSE 10A/400V GRL - Fuse

2908358

<https://www.phoenixcontact.com/us/products/2908358>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fuse, nominal current: 10 A, length: 31.8 mm, diameter: 6.35 mm



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2908358 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | CM24 |
| Product key | CMUEZ9 |
| GTIN | 4055626294773 |
| Weight per piece (including packing) | 4.9 g |
| Weight per piece (excluding packing) | 4.8 g |
| Customs tariff number | 85361010 |
| Country of origin | CN |

FUSE 10A/400V GRL - Fuse

2908358

<https://www.phoenixcontact.com/us/products/2908358>



Technical data

Product properties

| | |
|--------------|------|
| Product type | Fuse |
|--------------|------|

Electrical properties

| | |
|-------------------------|-----------|
| Tripping characteristic | fast-blow |
| Nominal voltage U_N | 400 V |
| Nominal current I_N | 10 A |
| Fuse | Fuse |

Dimensions

| | |
|------------|-------------|
| Dimensions | 6.2 x 32 mm |
|------------|-------------|

FUSE 10A/400V GRL - Fuse



2908358

<https://www.phoenixcontact.com/us/products/2908358>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2908358>



EAC

Approval ID: RU C-DE.BL08.B.00724

FUSE 10A/400V GRL - Fuse

2908358

<https://www.phoenixcontact.com/us/products/2908358>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27142008 |
| ECLASS-15.0 | 27142008 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002298 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

FUSE 10A/400V GRL - Fuse



2908358

<https://www.phoenixcontact.com/us/products/2908358>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com