

UM-SE 1 BK - Lateral element

2909824

<https://www.phoenixcontact.com/us/products/2909824>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Side element, for closing both ends of the base element UM-BEFE



The figure shows a green version

Commercial data

Item number	2909824
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC13
Product key	ACHDDA
GTIN	4017918412975
Weight per piece (including packing)	2.84 g
Weight per piece (excluding packing)	2.84 g
Customs tariff number	85369010
Country of origin	PL

UM-SE 1 BK - Lateral element



2909824

<https://www.phoenixcontact.com/us/products/2909824>

Technical data

Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing type	Plug-in module DIN rail-mount base
Housing series	UM
Ventilation openings present	no

Material specifications

Color (Side element)	black (RAL 9005)
Material Lateral element	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

PCB data

Number of PCB holders	1
-----------------------	---

Mounting

Mounting type	Latching
---------------	----------

UM-SE 1 BK - Lateral element



2909824

<https://www.phoenixcontact.com/us/products/2909824>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2909824>



UL Recognized

Approval ID: E240868

UM-SE 1 BK - Lateral element



2909824

<https://www.phoenixcontact.com/us/products/2909824>

Classifications

ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM-SE 1 BK - Lateral element



2909824

<https://www.phoenixcontact.com/us/products/2909824>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com