

PH 4/7 - Cable housing



3000740

<https://www.phoenixcontact.com/us/products/3000740>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable housing, pitch: 6.2 mm, width: 43.4 mm, height: 52.3 mm, number of positions: 7, color: gray

Your advantages

- Can be aligned without any loss of pitch
- Robust cable housing for strain relief on connecting cables
- Additional scope for marking plugs

Commercial data

Item number	3000740
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE22
Product key	BE224Z
GTIN	4046356688765
Weight per piece (including packing)	18.412 g
Weight per piece (excluding packing)	18.412 g
Customs tariff number	39269097
Country of origin	PL

PH 4/7 - Cable housing



3000740

<https://www.phoenixcontact.com/us/products/3000740>

Technical data

Product properties

Product type	Cable housing
Number of positions	7
Pitch	6.2 mm

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Dimensions

Width	43.4 mm
Height	52.3 mm
Pitch	6.2 mm

PH 4/7 - Cable housing

3000740

<https://www.phoenixcontact.com/us/products/3000740>



Classifications

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

PH 4/7 - Cable housing



3000740

<https://www.phoenixcontact.com/us/products/3000740>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com