

D-ZFKK 2,5-MT - End cover



3024151

<https://www.phoenixcontact.com/us/products/3024151>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, width: 2 mm, height: 41.2 mm, color: gray



Commercial data

Item number	3024151
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE29
Product key	BE2Z1X
GTIN	4017918130138
Weight per piece (including packing)	5 g
Weight per piece (excluding packing)	4.75 g
Customs tariff number	85389099
Country of origin	DE

D-ZFKK 2,5-MT - End cover



3024151

<https://www.phoenixcontact.com/us/products/3024151>

Technical data

Product properties

Product type	End cover
--------------	-----------

Material specifications

Color	gray
Flammability rating according to UL 94	V0
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	27,5 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Dimensions

Width	2 mm
Height	41.2 mm

D-ZFKK 2,5-MT - End cover



3024151

<https://www.phoenixcontact.com/us/products/3024151>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com