

AB-SK/E - Support bracket



3026476

<https://www.phoenixcontact.com/us/products/3026476>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Support bracket, Bracket for busbars, set every 20 cm, depth: 20 mm, width: 56 mm, height: 10 mm, diameter: 4.5 mm, number of positions: 2, color: silver-colored, mounting type: Direct mounting



Your advantages

- Version for NS 35 DIN rail mounting
- T-shaped support brackets for space-saving direct mounting and free positioning on the mounting panel
- Suitable for SK 5 to SK 14, SKS 8, and SKS 14 shield connection clamps

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3026476 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE07 |
| Product key | BE7113 |
| GTIN | 4017918168001 |
| Weight per piece (including packing) | 18.77 g |
| Weight per piece (excluding packing) | 17.237 g |
| Customs tariff number | 76169990 |
| Country of origin | PL |

AB-SK/E - Support bracket

3026476

<https://www.phoenixcontact.com/us/products/3026476>



Technical data


Product properties

| | |
|---------------------|-----------------|
| Product type | Support bracket |
| Number of positions | 2 |

Electrical properties

| | |
|-----------------------|-----|
| Nominal current I_N | 0 A |
|-----------------------|-----|

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 56 mm |
| Height | 10 mm |
| Depth | 20 mm |
| Diameter | 4.5 mm |

Material specifications

| | |
|---------------------|----------------|
| Color | silver-colored |
| Material | Aluminum |
| Insulating material | PA |

Mounting

| | |
|---------------|-----------------|
| Mounting type | Direct mounting |
|---------------|-----------------|


AB-SK/E - Support bracket

3026476

<https://www.phoenixcontact.com/us/products/3026476>



Drawings



AB-SK/E - Support bracket

3026476

<https://www.phoenixcontact.com/us/products/3026476>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27400607 |
| ECLASS-15.0 | 27400607 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001166 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

AB-SK/E - Support bracket



3026476

<https://www.phoenixcontact.com/us/products/3026476>

Environmental product compliance

EU RoHS

| | |
|---|---------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(b), 6(b)-II |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 658c4927-4542-4fea-a036-f67bcb435006 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.101 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com