

# FBS 1/3/5/7-8 - Plug-in bridge



3030396

<https://www.phoenixcontact.com/us/products/3030396>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in bridge, pitch: 8.2 mm, number of positions: 7, nominal current: 24 A, pin assignment: 1, 3, 5, 7, color: red

## Commercial data

Item number	3030396
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE29
Product key	BE2Z2X
GTIN	4055626007359
Weight per piece (including packing)	11.46 g
Weight per piece (excluding packing)	9.99 g
Customs tariff number	85366990
Country of origin	PL

## Technical data

### Notes

Note on application	Version with single- or double-sided cutting edge. Please keep in mind the possible impact on touch protection as well as air clearances and creepage distances.
---------------------	--

### Product properties

Product type	Plug-in bridge
Number of positions	7
Pitch	8.2 mm

### Electrical properties

Maximum load current	24 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

### Connection data

Maximum load current	24 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

### Dimensions

Width	55.7 mm
Height	29.6 mm
Pitch	8.2 mm

### Material specifications

Color	red (RAL 3001)
Material	Copper
Flammability rating according to UL 94	V0
Insulating material	PA

### Mechanical properties

#### Technical data

Pin assignment	1, 3, 5, 7
----------------	------------

### Mounting

Mounting type	Plug-in mounting
---------------	------------------

# FBS 1/3/5/7-8 - Plug-in bridge

3030396

<https://www.phoenixcontact.com/us/products/3030396>



## Classifications

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FBS 1/3/5/7-8 - Plug-in bridge



3030396

<https://www.phoenixcontact.com/us/products/3030396>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)