

# CEC 2,5 - Filler plug

3062757

<https://www.phoenixcontact.com/us/products/3062757>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover for conductor shaft, 10-pos., for spring cage terminal blocks (ST) and terminal blocks with push-in technology (PT) with a width of 5.2 mm

## Commercial data

Item number	3062757
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE29
Product key	BE2ZWX
GTIN	4046356661003
Weight per piece (including packing)	0.174 g
Weight per piece (excluding packing)	0.126 g
Customs tariff number	39269097
Country of origin	DE

# CEC 2,5 - Filler plug

3062757

<https://www.phoenixcontact.com/us/products/3062757>



## Technical data

### Product properties

Product type	Filler plug
--------------	-------------

### Marking

Number of individual labels	10
Number of individual labels per row	10

### Dimensions

Width	4.80 mm
Height	5.52 mm
Depth	8.00 mm
Length	5.3 mm

### Material specifications

Color	yellow (RAL 1018)
Material	PA 6.6
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

# CEC 2,5 - Filler plug

3062757

<https://www.phoenixcontact.com/us/products/3062757>



## Classifications

### ECLASS

ECLASS-13.0	27281107
ECLASS-15.0	27281107

### ETIM

ETIM 10.0	EC001777
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# CEC 2,5 - Filler plug



3062757

<https://www.phoenixcontact.com/us/products/3062757>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.004 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)