

# PSBJ 6-T YE - Test plug strip



3070326

<https://www.phoenixcontact.com/us/products/3070326>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Test plug strip, number of positions: 1, color: yellow



## Commercial data

Item number	3070326
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z3X
GTIN	4046356870856
Weight per piece (including packing)	5.62 g
Weight per piece (excluding packing)	5.62 g
Customs tariff number	85366990
Country of origin	PL

# PSBJ 6-T YE - Test plug strip

3070326

<https://www.phoenixcontact.com/us/products/3070326>



## Technical data

### Product properties

Product type	Test plug terminal block
Number of positions	1

### Connection data

Test socket torque	M3
Connection method	Screw connection

### Dimensions

Dimensional drawing	
Width	6 mm
Height	6 mm
Depth	15 mm
Screw thread	M3

### Material specifications

Color	yellow (RAL 1018)
-------	-------------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Mounting

Screw thread	M3
--------------	----


# PSBJ 6-T YE - Test plug strip

3070326

<https://www.phoenixcontact.com/us/products/3070326>



## Drawings



# PSBJ 6-T YE - Test plug strip



3070326

<https://www.phoenixcontact.com/us/products/3070326>

## Classifications

### ECLASS

ECLASS-13.0	27250304
ECLASS-15.0	27250304

### ETIM

ETIM 10.0	EC002555
-----------	----------

### UNSPSC

UNSPSC 21.0	20122000
-------------	----------

# PSBJ 6-T YE - Test plug strip



3070326

<https://www.phoenixcontact.com/us/products/3070326>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	332eb7ae-f542-4d42-9fcd-f90503a356a6

### EF3.1 Climate Change

CO2e kg	0.08 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)