

PSBJ 6-T VT - Test plug strip

3070328

<https://www.phoenixcontact.com/us/products/3070328>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Test plug strip, number of positions: 1, color: violet



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3070328 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE19 |
| Product key | BE1Z3X |
| GTIN | 4046356870870 |
| Weight per piece (including packing) | 5.69 g |
| Weight per piece (excluding packing) | 5.5 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

PSBJ 6-T VT - Test plug strip

3070328

<https://www.phoenixcontact.com/us/products/3070328>



Technical data

Product properties

| | |
|---------------------|--------------------------|
| Product type | Test plug terminal block |
| Number of positions | 1 |

Connection data

| | |
|--------------------|------------------|
| Test socket torque | M3 |
| Connection method | Screw connection |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 6 mm |
| Height | 6 mm |
| Depth | 15 mm |
| Screw thread | M3 |

Material specifications

| | |
|-------|-------------------|
| Color | violet (RAL 4005) |
|-------|-------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Mounting

| | |
|--------------|----|
| Screw thread | M3 |
|--------------|----|

PSBJ 6-T VT - Test plug strip

3070328

<https://www.phoenixcontact.com/us/products/3070328>



Drawings



PSBJ 6-T VT - Test plug strip



3070328

<https://www.phoenixcontact.com/us/products/3070328>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250304 |
| ECLASS-15.0 | 27250304 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002555 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 20122000 |
|-------------|----------|

PSBJ 6-T VT - Test plug strip



3070328

<https://www.phoenixcontact.com/us/products/3070328>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | a337746d-83e6-49ce-a43d-3683f4f26d9e |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.085 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com