

# VS-PT 10,3-HESI 16 - Connection pin

3062157

<https://www.phoenixcontact.com/us/products/3062157>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connection pin, for combining multiple safety levers. Used with fuse carriers without spacer.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3062157       |
| Packing unit                         | 1 pc          |
| Sales key                            | BE29          |
| Product key                          | BE2ZWX        |
| GTIN                                 | 4055626056890 |
| Weight per piece (including packing) | 0.255 g       |
| Weight per piece (excluding packing) | 0.255 g       |
| Customs tariff number                | 85389099      |
| Country of origin                    | CN            |

# VS-PT 10,3-HESI 16 - Connection pin



3062157

<https://www.phoenixcontact.com/us/products/3062157>

## Technical data

### Product properties

|              |        |
|--------------|--------|
| Product type | Bridge |
|--------------|--------|

### Dimensions

|          |        |
|----------|--------|
| Width    | 16 mm  |
| Diameter | 1.6 mm |

### Material specifications

|          |                   |
|----------|-------------------|
| Color    | silver-colored    |
| Material | Steel, galvanized |

# VS-PT 10,3-HESI 16 - Connection pin



3062157

<https://www.phoenixcontact.com/us/products/3062157>

## Classifications

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# VS-PT 10,3-HESI 16 - Connection pin



3062157

<https://www.phoenixcontact.com/us/products/3062157>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)