

TMB-QT 2,5/20-B 244 - Assembled cable connectors



3207761

<https://www.phoenixcontact.com/us/products/3207761>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled cable connectors

Commercial data

Item number	3207761
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF12
Product key	AF8EAA
GTIN	4046356058018
Weight per piece (including packing)	273.8 g
Weight per piece (excluding packing)	273.8 g
Customs tariff number	85444290
Country of origin	PL

TMB-QT 2,5/20-B 244 - Assembled cable connectors





3207761


<https://www.phoenixcontact.com/us/products/3207761>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3207761>

 CSA Approval ID: 13631				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
C	600 V	20 A	- 14	-

 UL Recognized Approval ID: E118976				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine	600 V	20 A	- 14	-

 IECEE CB Scheme Approval ID: DE1-64129				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine	800 V	20 A	-	-

 VDE report with production monitoring Approval ID: 40013075				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine	800 V	20 A	-	2.5

TMB-QT 2,5/20-B 244 - Assembled cable connectors



3207761

<https://www.phoenixcontact.com/us/products/3207761>

Classifications

ECLASS

ECLASS-13.0	27060390
ECLASS-15.0	27061801

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

TMB-QT 2,5/20-B 244 - Assembled cable connectors



3207761

<https://www.phoenixcontact.com/us/products/3207761>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com