

PR 1,5/S/2 - Latching

3212895

<https://www.phoenixcontact.com/us/products/3212895>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Latching, width: 6.8 mm, height: 28.9 mm, number of positions: 2, color: orange

Your advantages

- Can be used in all plug versions
- Snapped into the outside of the plug housing and hooks onto the terminal block housing when the plug is snapped on

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3212895 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE22 |
| Product key | BE224Z |
| GTIN | 4046356566032 |
| Weight per piece (including packing) | 0.59 g |
| Weight per piece (excluding packing) | 0.535 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

PR 1,5/S/2 - Latching

3212895

<https://www.phoenixcontact.com/us/products/3212895>



Technical data

Product properties

| | |
|---------------------|-------------------|
| Product type | Mounting material |
| Number of positions | 2 |

Dimensions

| | |
|--------|---------|
| Width | 6.8 mm |
| Height | 28.9 mm |

Material specifications

| | |
|--|-------------------|
| Color | orange (RAL 2003) |
| Material | PA-GF |
| Flammability rating according to UL 94 | HB |

PR 1,5/S/2 - Latching

3212895

<https://www.phoenixcontact.com/us/products/3212895>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27141190 |
| ECLASS-15.0 | 27250190 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002848 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.001 kg CO2e |
|---------|---------------|