

# WP-BASE HF 9-10 - Hose clamp

3240965

<https://www.phoenixcontact.com/us/products/3240965>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Hose clamp, material: Steel, galvanized, color: black/silver

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3240965       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BF68          |
| Product key                          | AF7DSA        |
| GTIN                                 | 4046356710732 |
| Weight per piece (including packing) | 6.04 g        |
| Weight per piece (excluding packing) | 5.65 g        |
| Customs tariff number                | 39174000      |
| Country of origin                    | DE            |

# WP-BASE HF 9-10 - Hose clamp



3240965

<https://www.phoenixcontact.com/us/products/3240965>

## Technical data

### Product properties

|              |                   |
|--------------|-------------------|
| Product type | Mounting material |
|--------------|-------------------|

### Dimensions

|               |        |
|---------------|--------|
| Diameter      | 10 mm  |
| Hole diameter | 4.5 mm |

### Material specifications

|            |                   |
|------------|-------------------|
| Material   | Steel, galvanized |
| Components | halogen-free      |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

### Mounting

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

# WP-BASE HF 9-10 - Hose clamp



3240965

<https://www.phoenixcontact.com/us/products/3240965>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-15.0 | 27430315 |
| ECLASS-13.0 | 27430315 |

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31162900 |
|-------------|----------|

# WP-BASE HF 9-10 - Hose clamp



3240965

<https://www.phoenixcontact.com/us/products/3240965>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |
| EF3.1 Climate Change                    |                                          |
| CO2e kg                                 | 0.255 kg CO2e                            |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)