

# WP-CN BRASS M16 - Counter nut

3241147

<https://www.phoenixcontact.com/us/products/3241147>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads M16, color: silver-colored



## Your advantages

- The brass counter nuts are used to lock protective hose screw connections in the case of bore holes without a thread.
- Metric thread in accordance with EN 50262

## Commercial data

Item number	3241147
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356785532
Weight per piece (including packing)	2.784 g
Weight per piece (excluding packing)	2.784 g
Customs tariff number	74153300
Country of origin	DE

# WP-CN BRASS M16 - Counter nut



3241147

<https://www.phoenixcontact.com/us/products/3241147>

## Technical data

### Product properties

Product type	Flat nut
Thread type	M16

### Dimensions

Height	2.8 mm
Thread type connection side	M16

### Material specifications

Material	Brass, nickel-plated
----------	----------------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 200 °C
---------------------------------	-------------------

# WP-CN BRASS M16 - Counter nut



3241147

<https://www.phoenixcontact.com/us/products/3241147>

## Classifications

### ECLASS

ECLASS-13.0	27140807
ECLASS-15.0	27140807

### ETIM

ETIM 10.0	EC003608
-----------	----------

### UNSPSC

UNSPSC 21.0	31161700
-------------	----------

# WP-CN BRASS M16 - Counter nut



3241147

<https://www.phoenixcontact.com/us/products/3241147>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	14b139cd-7d0c-468e-8d80-c3ae8e22e93c

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)