

WP-FS HF IP68 PG21 - Flat gasket



3241184

<https://www.phoenixcontact.com/us/products/3241184>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Flat gasket, material: Centellen, degree of protection: IP68, color: green, inside diameter: 27 mm



Your advantages

- The Centellen flat sealing rings are used to seal protective hose screw connections on uneven surfaces
- IP68 degree of protection
- Resistant to oil, seal against dust and water, UV resistant, halogen-free, high mechanical stability

Commercial data

Item number	3241184
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356785907
Weight per piece (including packing)	1.864 g
Weight per piece (excluding packing)	1.766 g
Customs tariff number	68159900
Country of origin	DE

WP-FS HF IP68 PG21 - Flat gasket



3241184

<https://www.phoenixcontact.com/us/products/3241184>

Technical data

Product properties

Product type	Seal
Thread type	Pg21

Dimensions

Height	2.5 mm
Diameter	34 mm
Panel thickness	2.5 mm

Internal dimensions

Internal diameter	27 mm
-------------------	-------

Material specifications

Material	Centellen
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-50 °C ... 200 °C

WP-FS HF IP68 PG21 - Flat gasket



3241184

<https://www.phoenixcontact.com/us/products/3241184>

Classifications

ECLASS

ECLASS-13.0	27430319
ECLASS-15.0	27430319

ETIM

ETIM 10.0	EC001181
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

WP-FS HF IP68 PG21 - Flat gasket



3241184

<https://www.phoenixcontact.com/us/products/3241184>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com