

LB SCHRAUBE MIT ISOL. BK - Bridge screw



5031414

<https://www.phoenixcontact.com/us/products/5031414>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bridge screw, M3, length: 30 mm, color: black



Commercial data

Item number	5031414
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918245160
Weight per piece (including packing)	1.35 g
Weight per piece (excluding packing)	1.373 g
Customs tariff number	74153300
Country of origin	PL

LB SCHRAUBE MIT ISOL. BK - Bridge screw



5031414

<https://www.phoenixcontact.com/us/products/5031414>

Technical data

Product properties

Product type	Mounting material
--------------	-------------------

Dimensions

Width	4.75 mm
Height	30.3 mm
Length	30.3 mm

Material specifications

Color	black (RAL 9005)
Material	Brass, nickel-plated
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

LB SCHRAUBE MIT ISOL. BK - Bridge screw



5031414

<https://www.phoenixcontact.com/us/products/5031414>

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 9.0	EC000489
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

LB SCHRAUBE MIT ISOL. BK - Bridge screw



5031414

<https://www.phoenixcontact.com/us/products/5031414>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com