

# D-BT 1,25 - End cover

3281120

<https://www.phoenixcontact.com/us/products/3281120>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, width: 3.5 mm, height: 26 mm, color: black



## Commercial data

Item number	3281120
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE59
Product key	BE5Z1X
GTIN	4055626119182
Weight per piece (including packing)	2.05 g
Weight per piece (excluding packing)	2.046 g
Customs tariff number	85389099
Country of origin	IN

# D-BT 1,25 - End cover



3281120

<https://www.phoenixcontact.com/us/products/3281120>

## Technical data

### Product properties

Product type	End cover
--------------	-----------

### Insulation characteristics

Overvoltage category	III
----------------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Material specifications

Color	black
Material	PC
Flammability rating according to UL 94	V0
Insulating material group	IIIa

### Dimensions

Width	3.5 mm
End cover width	3.5 mm
Height	26 mm

# D-BT 1,25 - End cover

3281120

<https://www.phoenixcontact.com/us/products/3281120>



## Classifications

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# D-BT 1,25 - End cover



3281120

<https://www.phoenixcontact.com/us/products/3281120>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)