

UMK-2FLK 14/16/BFI/120AC - Interface module



5602280

<https://www.phoenixcontact.com/us/products/5602280>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse module 1x 14-position

Commercial data

Item number	5602280
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK2BZZ
GTIN	4046356688338
Weight per piece (including packing)	33.33 g
Weight per piece (excluding packing)	33.33 g
Customs tariff number	85369010
Country of origin	US

UMK-2FLK 14/16/BFI/120AC - Interface module



5602280

<https://www.phoenixcontact.com/us/products/5602280>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	14

Connection data

Number of connections	1
Number of positions	14

Signaling

Status display	no
Status display present	yes, if the fuse fails

Dimensions

Item dimensions

Width	135.2 mm
Height	77 mm
Depth	58 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	Polyamide PA non-reinforced

Mounting

Mounting position	any
-------------------	-----

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

UMK-2FLK 14/16/BFI/120AC - Interface module



5602280

<https://www.phoenixcontact.com/us/products/5602280>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

5602280

<https://www.phoenixcontact.com/us/products/5602280>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com