

# EMG 30-SD/US/15A - Socket



5604253

<https://www.phoenixcontact.com/us/products/5604253>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Socket, color: black

## Commercial data

Item number	5604253
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE76
Product key	BE7613
GTIN	4046356683425
Weight per piece (including packing)	59.6 g
Weight per piece (excluding packing)	59.6 g
Customs tariff number	85369010
Country of origin	US

## Technical data

### Notes

#### Trade restriction

CE note	The products are offered exclusively for export outside the EU and the European Economic Area.
---------	--

### Product properties

Product type	Socket
For country-specific use in	USA
	Canada
	China
	Japan
	Mexico
	Peru
	Saudi Arabia
	Taiwan
	Thailand
	Phillipines
	Venezuela
Vietnam	

### Dimensions

Width	30 mm
Height	75 mm
Depth	54 mm

### Material specifications

Color	black
Insulating material	PVC 94 V0

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C

# EMG 30-SD/US/15A - Socket





5604253

<https://www.phoenixcontact.com/us/products/5604253>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/5604253>

 <b>UL Listed</b> Approval ID: E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	120 V	15 A	30 - 10	30 - 10

 <b>cUL Listed</b> Approval ID: E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	120 V	15 A	30 - 10	-

# EMG 30-SD/US/15A - Socket



5604253

<https://www.phoenixcontact.com/us/products/5604253>

## Classifications

### ECLASS

ECLASS-13.0

27142305

### ETIM

ETIM 9.0

EC001663

# EMG 30-SD/US/15A - Socket



5604253

<https://www.phoenixcontact.com/us/products/5604253>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)