

## Screwdriver - SF-SL 0,4X2,5-75 - 1212547

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Screwdriver, slot-headed, size: 0.4 x 2.5 x 75 mm, 2-component grip, with non-slip grip

### Your advantages

- The tools feature ergonomic two-component safety handles
- Large contact surface of blades inside screw head

### Key Commercial Data

Packing unit	10 pc
GTIN	 4 046356 589826
GTIN	4046356589826

### Technical data

#### Dimensions

Length (b)	145 mm
Width (a)	22 mm
Blade thickness	0.4 mm
Blade width	2.5 mm
Blade height	75 mm
Wrench size	0 mm

#### General

Type	Bladed
Material	alloyed tool steel
Test standard	DIN/ISO 2380-1

#### Standards and Regulations

Test standard	DIN/ISO 2380-1
---------------	----------------

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Drawings

# Screwdriver - SF-SL 0,4X2,5-75 - 1212547

Pictogram



## Classifications

### eCl@ss

eCl@ss 10.0.1	21040407
eCl@ss 11.0	21040407
eCl@ss 4.0	21040400
eCl@ss 4.1	21040400
eCl@ss 5.0	21040400
eCl@ss 5.1	21040400
eCl@ss 6.0	21040400
eCl@ss 7.0	21040407
eCl@ss 9.0	21040407

### ETIM

ETIM 2.0	EC000158
ETIM 3.0	EC000158
ETIM 4.0	EC000158
ETIM 6.0	EC000158
ETIM 7.0	EC000158

### UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701
UNSPSC 18.0	27111701
UNSPSC 19.0	27111701
UNSPSC 20.0	27111701

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

## Screwdriver - SF-SL 0,4X2,5-75 - 1212547

### Approvals

#### Approval details

EAC		RU C- DE.AI30.B.01750
-----	---	--------------------------

Phoenix Contact 2022 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>