

# WP-BASE C PA HF 28,2 BK - Hose holder with cover



3240962

<https://www.phoenixcontact.com/us/products/3240962>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Hose holder with cover, material: PA, color: black, flammability rating in acc. with UL 94: V2



## Commercial data

Item number	3240962
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356710701
Weight per piece (including packing)	9.148 g
Weight per piece (excluding packing)	7.024 g
Customs tariff number	39174000
Country of origin	DE

# WP-BASE C PA HF 28,2 BK - Hose holder with cover



3240962

<https://www.phoenixcontact.com/us/products/3240962>

## Technical data

### Product properties

Product type	Mounting material
--------------	-------------------

### Dimensions

Diameter	28.5 mm
Hole diameter	6.5 mm

### Material specifications

Material	PA
Flammability rating according to UL 94	V2
Components	halogen-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

### Mounting

Mounting type	Screw mounting
---------------	----------------

# WP-BASE C PA HF 28,2 BK - Hose holder with cover



3240962

<https://www.phoenixcontact.com/us/products/3240962>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240962>



**UL Recognized**  
Approval ID: E86359

# WP-BASE C PA HF 28,2 BK - Hose holder with cover



3240962

<https://www.phoenixcontact.com/us/products/3240962>

## Classifications

### ECLASS

ECLASS-13.0	27430315
ECLASS-15.0	27430315

### UNSPSC

UNSPSC 21.0	31162900
-------------	----------

# WP-BASE C PA HF 28,2 BK - Hose holder with cover



3240962

<https://www.phoenixcontact.com/us/products/3240962>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.618 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)