

D-SSK 0525 KER - End cover

0201061

<https://www.phoenixcontact.com/us/products/0201061>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, length: 38 mm, width: 4.2 mm, color: gray, insulation material: ceramic



Commercial data

Item number	0201061
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE19
Product key	BE1Z1X
GTIN	4017918098681
Weight per piece (including packing)	17.52 g
Weight per piece (excluding packing)	15.772 g
Customs tariff number	85389099
Country of origin	DE

D-SSK 0525 KER - End cover



0201061

<https://www.phoenixcontact.com/us/products/0201061>

Technical data

Product properties

Product type	End cover
--------------	-----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 180 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	cream (RAL 9001)
Flammability rating according to UL 94	V0

Dimensions

Width	4 mm
Height	38 mm
Depth	44.5 mm

D-SSK 0525 KER - End cover



0201061

<https://www.phoenixcontact.com/us/products/0201061>

Classifications

ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

ETIM

ETIM 10.0	EC000886
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

D-SSK 0525 KER - End cover



0201061

<https://www.phoenixcontact.com/us/products/0201061>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com