

# MPS-IH RD - Insulating sleeve



0201676

<https://www.phoenixcontact.com/us/products/0201676>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insulating sleeve, color: red



## Your advantages

- Two-piece test plug for individual plug color combinations
- The test plugs are inserted in the function shaft of the terminal blocks from the CLIPLINE complete system or in the test pick-offs provided

## Commercial data

Item number	0201676
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z3X
GTIN	4017918098155
Weight per piece (including packing)	0.51 g
Weight per piece (excluding packing)	0.269 g
Customs tariff number	85472000
Country of origin	PL

# MPS-IH RD - Insulating sleeve



0201676

<https://www.phoenixcontact.com/us/products/0201676>

## Technical data

### Product properties

Product type	Insulating sleeve
--------------	-------------------

### Connection data

Connection method	Spring-cage connection
-------------------	------------------------

### Dimensions

Width	4.6 mm
Height	27.5 mm
Depth	27.5 mm

### Material specifications

Color	red (RAL 3001)
Material	PA
Flammability rating according to UL 94	V2
Insulating material	PA
Static insulating material application in cold	-40 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Relative insulation material temperature index (Elec., UL 746 B)	125 °C

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

# MPS-IH RD - Insulating sleeve



0201676

<https://www.phoenixcontact.com/us/products/0201676>

## Classifications

### ECLASS

ECLASS-13.0	27141192
ECLASS-15.0	27141192

### ETIM

ETIM 10.0	EC004592
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# MPS-IH RD - Insulating sleeve



0201676

<https://www.phoenixcontact.com/us/products/0201676>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.004 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)