

FBI 10- 8 - Fixed bridge

0203263

<https://www.phoenixcontact.com/us/products/0203263>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fixed bridge, pitch: 8 mm, number of positions: 10, color: silver-colored



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0203263 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE19 |
| Product key | BE1Z2X |
| GTIN | 4017918099053 |
| Weight per piece (including packing) | 25.5 g |
| Weight per piece (excluding packing) | 25 g |
| Customs tariff number | 85369095 |
| Country of origin | IN |

FBI 10- 8 - Fixed bridge



0203263

<https://www.phoenixcontact.com/us/products/0203263>

Technical data

Product properties

| | |
|---------------------|--------------|
| Product type | Screw bridge |
| Number of positions | 10 |
| Pitch | 8 mm |

Dimensions

| | |
|-------|------|
| Pitch | 8 mm |
|-------|------|

Material specifications

| | |
|---------------------|----------------|
| Color | silver-colored |
| Material | Copper |
| Insulating material | PA |

Mounting

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

FBI 10- 8 - Fixed bridge



0203263

<https://www.phoenixcontact.com/us/products/0203263>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250303 |
| ECLASS-15.0 | 27250303 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000489 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

FBI 10- 8 - Fixed bridge



0203263

<https://www.phoenixcontact.com/us/products/0203263>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.439 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com