

# KSS 8 - Short-circuit connector

0311540

<https://www.phoenixcontact.com/us/products/0311540>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Short-circuit connector, pitch: 8 mm, number of positions: 2, color: black



## Commercial data

Item number	0311540
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z3X
GTIN	4017918001490
Weight per piece (including packing)	8.354 g
Weight per piece (excluding packing)	7.95 g
Customs tariff number	85366990
Country of origin	PL

# KSS 8 - Short-circuit connector



0311540

<https://www.phoenixcontact.com/us/products/0311540>

## Technical data

### Product properties

Product type	Short-circuit connector
Number of positions	2
Pitch	8 mm

### Dimensions

Pitch	8 mm
-------	------

### Material specifications

Color	black (RAL 9005)
Material	Copper
Flammability rating according to UL 94	V2
Insulating material	PA

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Mounting

Mounting type	Plug-in mounting
---------------	------------------

# KSS 8 - Short-circuit connector



0311540

<https://www.phoenixcontact.com/us/products/0311540>

## Classifications

### ECLASS

ECLASS-13.0

27250303

### ETIM

ETIM 9.0

EC000489

### UNSPSC

UNSPSC 21.0

39121400

# KSS 8 - Short-circuit connector



0311540

<https://www.phoenixcontact.com/us/products/0311540>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	73c59111-2e14-4a8f-bf16-6b2208b039ea

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)