

# EB 3- 8 OG - Insertion bridge

0710921

<https://www.phoenixcontact.com/us/products/0710921>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insertion bridge, 3-pos., fully insulated, color of the insulation material: orange



## Commercial data

Item number	0710921
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918479268
Weight per piece (including packing)	3.357 g
Weight per piece (excluding packing)	3.357 g
Customs tariff number	85366990
Country of origin	PL

# EB 3- 8 OG - Insertion bridge



0710921

<https://www.phoenixcontact.com/us/products/0710921>

## Technical data

### Product properties

Product type	Insertion bridge
Number of positions	3

### Material specifications

Color	orange (RAL 2003)
-------	-------------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

# EB 3- 8 OG - Insertion bridge



0710921

<https://www.phoenixcontact.com/us/products/0710921>

## Classifications

### ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

### ETIM

ETIM 10.0	EC000489
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# EB 3- 8 OG - Insertion bridge



0710921

<https://www.phoenixcontact.com/us/products/0710921>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)